

Assembly instructions

Attach the absorber with four suitable screws using the supplied template to a sufficiently stable wall (assembly material is not supplied).



- High-quality processed acoustic module for lower to middle frequency ranges
- Efficiency:
250 Hz – 4000 Hz
- Absorption coefficient: 0.75
- Frame: 12 mm birch plywood, filled with mineral wool
- Surface: Combination of shredded wood chips and cement
- Optically pleasing fitting in existing interior
- easy assembly and disassembly due to fastening clips (not suitable for ceiling mounting)
- Frame dimensions:
600 mm × 600 mm × 100 mm
- Colour: cream
- Weight: 6 kg

This module is intended to be used to optimise the room acoustics. Any other use or use under other operating conditions is considered to be improper and may result in personal injury or property damage. No liability will be assumed for damages resulting from improper use.



Ensure that plastic bags, packaging, etc. are properly disposed of and are not in the reach of babies and young children. Choking hazard!



For the packaging, environmentally friendly materials have been chosen that can be supplied to normal recycling. Ensure that plastic bags, packaging, etc. are properly disposed of. Do not just dispose these materials with your normal household waste, but make sure that they are fed to a recovery. Please follow the notes and markings on the packaging.